



DCS380N-XE

18V XR Li-Ion Reciprocating Saw

Selling Proposition

- Latest generation premium Reciprocating Saw featuring new XR Lithium Ion Technology
- Powerful & Highly Efficient PM58 DEWALT fan cooled motor with replaceable brushes, delivers fast cutting action up to 2,950 strokes per minute and 28.6 mm stroke length maximising user productivity
- High performance reciprocating mechanism and lightweight magnesium gearcase offer the user optimised power to weight ratio
- Intelligent variable speed trigger, lock-off switch and electronic motor brake for quick controlled cuts and enhanced work safety
- Lever-action keyless blade clamp for quick and easy blade changes
- 4-Position blade clamp allows for flush cutting and increased versatility

Standard Equipment

- Bare Unit

Warranty Specifications

- 3 Year Limited Warranty (Terms and Conditions Apply)
- 1 Year Free Service Contract
- 30 Day No Risk Satisfaction Guarantee

Specifications

Voltage	18 V
Power Output	560 Watts
No Load Stroke Rate	0-2950 spm
Stroke Length	28.6 mm
Weight	2.7 kg
Length	425 mm