

# MP 10080

# FIBOX

Enclosing innovations



Sample image

**Order symbol:** MP 10080

**Product nbr:** 8200080

**Description:** Mounting plate. for enclosures:

**Remarks:** 1035x835x300

**Including:**

**EAN:** 6418074050199

**EI. number:**

- Finland: 3424280
- Denmark: 8212018727
- Sweden: 2539847

Dimensions:	Height	Width	Depth
mm:	1000	800	3
inch:	39.37	31.5	0.12

#### Materials:

Material:

Base colour:

Cover colour:

Gasket material:

#### Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

#### Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

#### Certificates: