

## M18 FSX-OC | M18 FUEL™ Super SAWZALL™



- The M18 FUEL™ Super SAWZALL™ delivers the power to cut at the same speed as an equivalent AC reciprocating saw - with the ability to cut 150 pieces of 290 mm x 45 mm pine on one 12.0 Ah battery charge
- Next generation POWERSTATE™ brushless motor, REDLINK PLUS™ electronics and REDLITHIUM™-ION HIGH OUTPUT™ 12.0 Ah battery pack deliver superior performance, durability and run time in high demand applications
- Orbital action allows the saw to clear the cut of debris giving a faster cut in wood materials
- 3000 SPM with a 32 mm stroke length delivers fast and effortless cutting in a wide range of materials
- 5 variable speed settings from 1500 SPM to 3000 SPM to allow the correct speed to be set for the material being cut
- FIXTEC™ blade clamp for fast and easy blade changes without any key
- Durable metal rafter hang hook for work space management and safety

No load stroke rate (spm)	0 - 3000
Stroke length (mm)	32
Kit included	No batteries supplied, No charger supplied, Kitbox
Article Number	4933464724