


TAPD68BS LF14 - Break Stem Open

General Part Information	
Product Description	TAPD68BS LF14
Article Number	22050.00
Rivet Type	i Break Stem Open
Standard Bulk Pack Quantity	4000.00
Application / Features	i 



Geometry / Dimensions / Performance	
Head Style	i Large Flange
Body Diameter Ø (mm)	4.80
Body Length (mm)	11.00
Min. Grip Range (mm)	4.80
Max. Grip Range (mm)	6.40
Min. Hole Diameter (mm)	4.90
Max. Hole Diameter (mm)	5.00
Min. Flange Diameter (mm)	13.70
Max. Flange Diameter (mm)	14.30
Flange Thickness (mm)	2.00
Mandrel Diameter (mm)	2.64
Nominal Shear Strength (N)	2020.00
Nominal Tensile Strength (N)	2800.00

Material / Finish / Weight	
Body Material	i AlMg3.5
Mandrel Material	Steel
Finish	Clean
Weight per thousand (kg)	3.14