


9001KS46FB

selector switch Ø 30 - 3 position maintained -
long handle - black



Main

Range of product	Harmony 9001K
Product or component type	Selector switch
Component name	9001K
Bezel material	Chromium plated metal
Mounting diameter	30 mm
Operator position information	3 positions
Type of operator	Stay put
Shape of signaling unit head	Octagonal
Operator profile	Long handle
Cap/Operator or lens colour	Black
Contacts type and composition	Without contact block
Product compatibility	9001KA1 mounting on side 1 or 2

Complementary

Mechanical durability	500000 cycles
Product weight	0.172 kg

Environment

Standards	CSA C22-2 No 14 EN/IEC 60947-5-1 IEC 60947-1 IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Vibration resistance	7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
Class of protection against electric shock	Class II conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529 IP66 conforming to NF C 20-010
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 6
RoHS EUR status	Will be compliant
RoHS EUR conformity date	2Q2009

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.