


728B
bi-hex impact sockets, 3/4" female square drive, standard series, phosphated

UNI/ISO 2725 DIN 3129


	art.	Ø mm	Ø mm	L mm	Ø1 mm	A mm	Wt g
007280117	728B 17	17	28,5	50	38	9,6	230
007280119	728B 19	19	30	52	38	11,1	230
007280121	728B 21	21	32	52	38	11,7	240
007280122	728B 22	22	34	52	38	12,5	250
007280123	728B 23	23	35	52	38	12,7	250
007280124	728B 24	24	36	52	38	14	250
007280127	728B 27	27	40	52	40	15,8	280
007280129	728B 29	29	42	52	42	16,7	320
007280130	728B 30	30	44	52	44	16,7	370
007280132	728B 32	32	48	52	44	18,2	380
007280133	728B 33	33	50	56	44	19,1	410
007280134	728B 34	34	51	56	44	20	410
007280135	728B 35	35	52	56	44	20,1	470
007280136	728B 36	36	53,5	56	44	21,5	470
007280138	728B 38	38	56	56	44	22,3	470
007280141	728B 41	41	60	58	44	23	590
007280146	728B 46	46	67	63	44	23	770

