

har-SAB M8/6/3p M16/14p w/o LED



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 004 1010 000
Specification	har-SAB M8/6/3p M16/14p w/o LED
HARTING eCatalogue	https://harting.com/09070041010000

Identification

Series	Circular connectors M8
Element	Distribution boxes
Specification	Master cable M16, 14 poles

Version

Total number of ports	6
Number of contacts	3

Technical characteristics

Rated current	6 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-25 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	1
Circuit logic	PNP

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances Not contained

California Proposition 65 substances Yes

California Proposition 65 substances Nickel

Commercial data

Packaging size 1

Country of origin China

European customs tariff number 85444290

GTIN 5713140276734

eCl@ss 27440108 Passive Sensor-Actuator-Interface (with cable)

ETIM EC002585

UNSPSC 24.0 31251501