


Technical data sheet

Article number:
112-05219

T50I



Product Group	Cable Ties Polyamide 6.6 standard
Product Family	T-Series in PA66 natural
Material	Polyamide 6.6 (PA66)
Colour	Natural (NA)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	80.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Halogen-free	Yes
Length (L)	305.0 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	pack
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	No
Specifications	UL 62275
Thickness (T)	1.2 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E64139
UV-resistant acc. to ASTM D6779 (Yes/No)	No
Variant	Inside Serrated
Weight/Unit	0.0019 kg
Width (W)	4.6 mm

