

FEATURES

- **Nylon Material:** Provides excellent strength and flexibility for various applications
- **Non-Releasable Design:** Ensures a secure hold that won't loosen over time
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **High Tensile Strength:** Withstands up to 34 kg, offering robust support for heavy bundles
- **Fire Behaviour UL 94 V-2:** Meets safety standards for flammability
- **Maximum Bundle Diameter 70mm:** Accommodates large cable bundles
- **Operating Temperature up to 85°C:** Suitable for high-temperature environments

RS PRO Nylon Cable Tie, 280mm Non-Releasable

RS Stock No: 656-052



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a reliable Nylon Cable Tie designed for secure bundling and organisation of cables and wires. With a length of 280mm, this non-releasable cable tie is ideal for applications requiring a strong and durable fastening solution. Its UV resistance ensures longevity even in outdoor environments.

General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	34 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	280 mm
Material	Nylon
Maximum Bundle Diameter	70 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---