# **Product datasheet**

Specifications



### steady incandescent bulb - BA 15d -24 V AC/DC - <= 5 W

Local distributor code: 398229674

DL1EDBS

EAN Code: 3389119004435

#### Main

Range compatibility	Harmony XVM Optimum
Accessory / separate part category	Lighting accessory
Accessory / separate part type	Incandescent bulb
Accessory / separate part designation	Incandescent bulb
Accessory / separate part destination	Beacon and indicator bank
Bulb base	BA 15d
Signalling type	Steady
[Us] rated supply voltage	24 V AC/DC
Luminance	650 cd/m <sup>2</sup>
Sale per indivisible quantity	10

### Complementary

Maximum power dissipation in W	5 W
Net weight	0.007 kg

### **Packing Units**

PCE
1
1.000 cm
1.500 cm
4.000 cm
6.000 g
S01
140
15.000 cm
15.000 cm
40.000 cm
1.450 kg
P06
4480
75.000 cm

Package 3 Width	60.000 cm	
Package 3 Length	80.000 cm	
Package 3 Weight	54.000 kg	

## Logistical informations

Country of origin

ID

## **Contractual warranty**

Warranty

18 months

## Lenvironmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability  $\geq$ 

$\ensuremath{ \bigtriangledown \bigtriangledown }$ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	51

#### Use Better

Materials and Substances		
Packaging made with recycled cardboard	Yes	
Packaging without single use plastic	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
REACh Regulation	REACh Declaration	

#### **Use Again**

$^{igodoldoldoldoldoldoldoldoldoldoldoldoldol$	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins