

## Han-Eco 10A-Cover



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 46 010 5425                                                                |
| Specification      | Han-Eco 10A-Cover                                                             |
| HARTING eCatalogue | <a href="https://harting.com/19460105425">https://harting.com/19460105425</a> |

### Identification

|                              |                                                               |
|------------------------------|---------------------------------------------------------------|
| Category                     | Accessories                                                   |
| Series of hoods/housings     | Han-Eco® A                                                    |
| Type of accessory            | Protection cover                                              |
| Description of the accessory | for bulkhead mounted housings<br>for surface mounted housings |

### Version

|              |                      |
|--------------|----------------------|
| Size         | 10 A                 |
| Locking type | Single locking lever |

### Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Number of relockings                   | ≥500            |
| Degree of protection acc. to IEC 60529 | IP65            |

### Material properties

|                                           |                                          |
|-------------------------------------------|------------------------------------------|
| Material (hood/housing)                   | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)                     | RAL 9005 (jet black)                     |
| Material (seal)                           | NBR                                      |
| Material flammability class acc. to UL 94 | V-0                                      |
| RoHS                                      | compliant                                |
| ELV status                                | compliant                                |
| China RoHS                                | e                                        |



**Pushing Performance**  
Since 1945

## Material properties

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| REACH Annex XVII substances         | Not contained                       |
| REACH ANNEX XIV substances          | Not contained                       |
| REACH SVHC substances               | Not contained                       |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels  | R22 (HL 1-2)                        |
|                                     | R23 (HL 1-3)                        |

## Specifications and approvals

|                |                                                |
|----------------|------------------------------------------------|
| Specifications | IEC 61984                                      |
|                | EN 45545-2 Fire protection on railway vehicles |

## Commercial data

|                                |                                        |
|--------------------------------|----------------------------------------|
| Packaging size                 | 1                                      |
| Net weight                     | 26.2 g                                 |
| Country of origin              | Germany                                |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140192164                          |
| eCl@ss                         | 27440208 Cap for industrial connectors |
| ETIM                           | EC002314                               |
| UNSPSC 24.0                    | 39121467                               |