

Rexel Momentum M510 Micro Cut Paper Shredder

The power to shred more! The Momentum M510 paper shredder shreds up to 10 sheets (80 gsm) in to P-5 (2x15mm) micro cut pieces, with a 23L bin which holds 250 A4 sheets.



Attributes

- Shreds up to 10 sheets in one pass (80gsm)
- P-5 (2x15mm), 1 x A4 sheet into 2000 micro cut pieces
- 23L bin capacity, 250 A4 sheets
- Anti jam technology, shredder automatically stops and reverses when too much paper is inserted
- Easily shreds multiple documents, even with staples and paperclips on the corners
- Sleep mode after 2 minutes of non use
- Bin full indicator
- Ultra quiet operation < 60 DbA
- Touch panel operation for easy use
- 2 Year Warranty
- 2 Year Cutter Warranty



Specifications

Number	2104575
Colour	black
Dimensions (W x H x D)	370 x 465 x 279 mm
Cut Type	Micro Cut
Maximum Slot Entry Width (mm)	223
Run Time From Cold (min)	120
Run Time/Cool Down Time (min)	120/60
Shredded Particle Width mm	2x15
Security Level	P-5
Cutting Capacity sheets (70gsm paper)	11
Cutting Capacity sheets (80gsm paper)	10
Container/collection volume in l	23
Shreds	Paper, Paper clips & Staples
Power consumption (W)	350
Noise Level (dBA)	58
Period of Warranty (Years)	2
Weight	12500 g
Pallet quantity	18
EAN code	5028252523134