

ix Type B solder 5x2xAWG26 PVC 10m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 161 6A20 100
Specification	ix Type B solder 5x2xAWG26 PVC 10m
HARTING eCatalogue	https://harting.com/33481616A20100

Identification

Category	System cabling
Series	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® Type B
Connector 2	HARTING ix Industrial® Type B
Type of cable	Copper cable (round)

Version

Cable length	10 m
Number of cores	10
Core structure	10x AWG 26
Termination method	Solder termination
Coding	Type B

Technical characteristics

Rated current	1.5 A
Rated voltage	50 V AC 60 V DC
Limiting temperature	-30 ... +80 °C

Material properties

Material (cable)	PVC
------------------	-----



Pushing Performance
Since 1945

Material properties

Colour (cable) Grey

Specifications and approvals

Specifications IEC 61076-3-124

Commercial data

Packaging size 1

Country of origin Vietnam

European customs tariff number 85444290

GTIN 5713140260139

eCl@ss 27060390 Ready-made data cable (unspecified)

ETIM EC002599
