

8091SL
Lifting chain slings, 1 leg, self-locking hook, grade 8

CE

UNI EN 818-4

TECHNICAL DATA

- safety factor: 4
- chain-sling identification tag

ATTACHED CERTIFICATES

- Manufacturer's Certificate UNI EN818-4
- CE Declaration of Conformity

AVAILABLE CERTIFICATES

- Technical product specifications



	art.	 D mm	L m	WLL ton
080910201	8091SL D6-1	6*	1	1,12
080910202	8091SL D6-2	6*	2	1,12
080910203	8091SL D6-3	6*	3	1,12
080910204	8091SL D6-4	6*	4	1,12
080910221	8091SL D7-1	7*	1	1,5
080910222	8091SL D7-2	7*	2	1,5
080910223	8091SL D7-3	7*	3	1,5
080910224	8091SL D7-4	7*	4	1,5
080910241	8091SL D8-1	8*	1	2
080910242	8091SL D8-2	8*	2	2
080910243	8091SL D8-3	8*	3	2
080910244	8091SL D8-4	8*	4	2
080910251	8091SL D10-1	10*	1	3,15
080910252	8091SL D10-2	10*	2	3,15
080910253	8091SL D10-3	10*	3	3,15
080910254	8091SL D10-4	10*	4	3,15
080910330	8091SL	13	0,6	5,3
080910331	8091SL D13-1	13*	1	5,3
080910332	8091SL D13-2	13*	2	5,3
080910333	8091SL D13-3	13*	3	5,3
080910334	8091SL D13-4	13*	4	5,3
080910360	8091SL	16	0,6	8
080910361	8091SL D16-1	16*	1	8
080910362	8091SL D16-2	16*	2	8
080910363	8091SL D16-3	16*	3	8
080910364	8091SL D16-4	16*	4	8
080910401	8091SL D20-1	20	1	12,5
080910402	8091SL D20-2	20	2	12,5
080910403	8091SL D20-3	20	3	12,5
080910404	8091SL D20-4	20	4	12,5