



ENGLISH

Datasheet

RS Pro Steel Alloy Compression Spring, 110mm x 21.6mm, 0.99N/mm

RS Stock No: **121-242**



Product Details

RS Pro stainless steel alloy compression spring measures 110 x 21.6 mm and has a spring rate of 0.99 N/mm. It handles a load of 84.83 N at a minimum working length of 25.5 mm. This spring features right hand helix construction.

Features and Benefits

- Wire diameter ends up to 0.8 mm are squared and ungrounded
- Wire diameter ends 1 mm and over are squared and ground
- Manufactured with a right hand helix



Specifications:

Ends	Closed (Square)/Ground
Material	Steel Alloy
Free Length	110 mm
Load at Minimum Working Length	84.83 N
Minimum Working Length	25.5 mm
Outside Diameter	21.6 mm
Spring Rate	0.99 N/mm
Wire Diameter	1.6 mm