


AFFLEX LSOH H05Z1Z1-F

The easy strip low smoke zero halogen flex



CABLE DESCRIPTION

Conductor

Stranded copper class 5 according to IEC 60228

Insulation

Thermoplastic compound LSOH, type TI 6.

Separator

Easy strip tape to ensure quick and effortless sheath removal

Outer Sheath

White Thermoplastic compound, LSOH, type TM 7

Technical Data

Reference Standards EN 50525-3-11

Service temperature -10 + 70 °C

Rated voltage 300/500 V

AC Voltage test, 5 min at 2.0kV

Bending radius 4D

Key Features

- > Genuine FLEX (EN 50525-1)
- > Easy strip sheath: no sticking or jamming
- > Genuine low smoke, zero halogen and flame retardant

Fire Performance

- > Flame retardant: UNE EN 60332-1-2, IEC 60332-1-2
- > Fire retardant: UNE EN 60332-3-24, IEC 60332-3-24
- > Zero Halogen: UNE EN 50267-2-1, IEC 60754-1
- > Low Smoke: UNE EN 61034-2, IEC 61034-2
- > Acidic and corrosive gases: UNE EN 50267-2-2, IEC 60754-2

Approvals

- > HAR approved AENOR: EN 50525-3-11

Core Identification

Harmonised - standard

- ○ brown-blue
- ○ ○ brown-black-grey
- ○ ○ ○ blue-brown-black-grey

Non harmonised - to special order

- ○ red-black
- ○ ○ red-yellow-blue
- ○ ○ ○ black-red-yellow-blue



Temperature Range
-10 to 70 °C



Bending Radius
Fixed r=4D



Mechanical Impact
Medium



Fire Performance
UNE EN 60332-1-2
UNE EN 60332-3-24



Flexibility
Flexible



Halogen Free
UNE EN 50267-2-2



Low Smoke Emissions
UNE EN 61034-2

Nominal Cross Sectional Area mm ²	Insulation Thickness mm	Nominal Outer Sheath Thickness mm	Approx. Outer Diameter mm	Approx. Weight kg/km	Prysmian Code
---	----------------------------	--------------------------------------	------------------------------	-------------------------	---------------

Two Core

0.75	0.6	0.8	6.5	60	20163901
1.0	0.6	0.8	6.7	65	20163874

Three Core

0.75	0.6	0.8	6.8	70	20163902
1.0	0.6	0.8	7.1	78	20163875
1.5	0.7	0.9	8.3	107	20163876
2.5	0.8	1.1	10.1	167	20163880
4.0	0.8	1.2	11.3	227	20163881

Four Core

0.75	0.6	0.8	7.4	84	20163903
1.0	0.6	0.9	7.9	98	20163877
1.5	0.7	1.0	9.3	135	20163878
2.5	0.8	1.1	11.1	203	20163879
4.0	0.8	1.2	12.4	278	20163882

Five Core

0.75	0.6	0.9	8.3	103	20163904
------	-----	-----	-----	-----	----------

Current Rating

BS7671 Table 4F3A and 4F3B

Sales enquiries

Tel: 0845 767 8345
Fax: 023 8029 5465

UK Technical helpline

Tel: 0845 767 8345
Fax: 023 8029 5002

Prysmian Cables & Systems Limited

Chickenhall Lane
Eastleigh
Hampshire
SO50 6YU
United Kingdom
www.prysmiangroup.co.uk

For further information please see our dedicated Afumex Cables website:
www.afumexcables.co.uk

Overseas sales enquiries

Tel: +44 (0) 23 5029 5481
Fax: +44 (0) 23 8029 5465

Overseas technical

Tel: +44 (0) 23 8029 5481
Fax: +44 (0) 23 8029 5002

Information hotline

Tel: +44 (0) 23 8029 5029
Fax: +44 (0) 23 8029 5437



Should you have any concerns about unsafe, non-approved or counterfeit cable, please contact the ACI

Tel: 020 8946 6978
Email: report@aci.org.uk