

# Bosch D-Tect 120 Professional Detector



**BOSCH**  
Invented for life

## The intuitive radar scanner for all materials

- **Dual Power Source:** Can be operated both with 10.8 V LI battery and with standard alkaline batteries
- **Spot measurement** instead of procedural measurement enables detection on extremely small surfaces
- **Centre finder:** Visual direction guidance for precise locating of the object's centre



### Technical Data

Detectable materials	Water-filled plastic pipes, ferrous metals, non-ferrous metals, wooden studs, live cables
Max. detection depth	120 mm
Detection depth, steel, max.	120 mm
Detection depth, copper, max.	120 mm
Detection depth of live cables, max.	60 mm
Detection depth of wooden substructures, max.	38 mm



### Scope of Delivery

Alkaline batteries  
Battery adapter  
Carton (L-BOXX-ready)  
Quick-start card

Part Number	EAN Code	Order Code
0601081300	3165140780063	DTECT120