

FEATURES

- **Sintered Bronze Material:** Offers excellent wear resistance and durability.
- **Flanged Design:** Provides additional support and stability in applications.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **ISO 2795 and ISO 9001:2008 Certified:** Ensures compliance with international quality standards.

RS PRO 22.02 mm Flanged Plain Bearing

RS Stock No: 558-465



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 22.02 mm Flanged Plain Bearing is designed to provide reliable performance in various industrial applications. Made from high-quality sintered bronze, this bearing is ideal for reducing friction between moving parts, ensuring smooth operation and longevity.

General Specifications

Bore Size	22.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	28.05 mm
Width	30 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

