

Replacement Light Tower LED, BA15

46-584.1922

Distribution by
Rs-online



<https://www.rs-online.eao.com/component/46-58...>

Your product:



46-584.1922

Replacement Light Tower LED, BA15

Loading ...

OPERATING-/INDICATION PART

Illumination colour: White

ELECTRICAL CHARACTERISTICS

Operating voltage: 230 V AC -20% / +10%

Protection class: II, according to EN / IEC 61140

MECHANICAL CHARACTERISTICS

Weight: 0.007 kg

AMBIENT CONDITION

Operating temperature: - 25 °C ... + 70 °C

CERTIFICATE

Conformities: CE

Standards: EN 55015, EN 61000-3-2, EN 61000-3-3, EN 61547, IEC EN 62471

OTHER

Short Description:	Replacement Light Tower LED, BA15, Ø 15 mm x 38 mm, 230 V AC -20% / +10%
Titel Accessory:	Replacement Light Tower LED, BA15
Kind of illumination:	Single-LED
Dimension:	Ø 15 mm x 38 mm
Product attributes:	For Signal Light Tower