



### Main

Range	Resi9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L
Length in 18 mm modules	11



### Complementary

Number of ways	3 ways 3 L
Poles configuration for 1 way	1 x 3P
Connection pitch	18 mm
Connector type	Fork
Distance between way	54 mm
Marking	L1 L2 L3
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	63 A at 40 °C
[Ue] rated operational voltage	400 V AC Ph/Ph
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting mode	Horizontal
Mounting location	Bottom on biconnect
9 mm pitches	22
Width	198 mm
Colour	White (RAL 9003)
Range compatibility	Acti 9 K60 Resi9 MCB Resi9 RCBO Resi9 RCCB Resi9 SWITCH

### Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins