
**TOLERANCE** UNLESS OTHERWISE SPECIFIED .X ±0.25 .XX ±0.13

.XXX ±0.05

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER ORIGINAL






**CURRENT RATING:** 2A AC/DC **VOLTAGE RATING:** 100V AC/DC TEMPERATURE RATING: -25°C ~ 85°C (CONTACT RESISTANCE: 10mΩ MAX.) HOUSING RESISTANCE:  $1000M\Omega$  min. WITHSTANDING VOLTAGE: 800V AC / 60s

**HOUSING MATERIAL:** NYLON PA66, UL94V-0





## 140 SERIES FEMALE CRIMP CONTACT HOUSING



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 140 Assembly	
DRAWN: C.B	DATE: April 3, 2020
CHECKED:	DATE:
SCALE: 5:1	SHEET 1 OF 1
DRAWING NUMBER: 140 Assembly	

DRAWING NUMBER: 140 Assembly ISSUE PART NUMBER: 140-506-210-011

