

FEATURES

- Glass clear transparency
- Excellent abrasion and corrosion properties
- Good flexibility
- EC compliant for food applications
- Suitable for use with alcohol, petrol, oils, greases and solvents
- Highly resistant to a wide range of acids and alkalis
- Manufactured from cadmium and silicone-free materials using a special low toxic

RS PRO PVC Flexible Tubing, Transparent, 48mm External Diameter, 15m Long, 432mm Bend Radius, Applications Various

RS Stock No.: 293-2066



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS Pro clear PVC hose is suitable for a wide range of applications such as for low-pressure food and general industrial based environments. The hose is manufactured from the highest quality, low-toxic materials to give excellent clarity, flexibility and durability over a wide temperature range. The highly flexible hose supports use in both open and tight spaces and with excellent corrosion and abrasion properties, this PVC hose is a durable and reliable tool in any application.

General Specifications

Material	PVC
Colour	Transparent
Reinforced	No
Application	Alcohol, Grease, Oil, Petrol, Solvent, General industrial applications; Scientific; Pharmaceutical; Medical

Mechanical Specifications

Inner Diameter	38mm
Outer Diameter	48mm
Length	15m
Bend Radius	432mm

Operation Environment Specifications

Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Maximum Working Pressure	5 bar

Approvals

Compliance/Certifications

RoHS compliant

Product Ref.	Size		Weight per coil kgs
	I.D.	O.D.	
Coil length 100m			
C02/04	2mm	4mm	1.2
C03/05	3mm	5mm	1.6
C03/06	3mm	6mm	2.6
C04/06	4mm	6mm	1.9
C04/07	4mm	7mm	3.2
C04/08	4mm	8mm	4.7
C05/07	5mm	7mm	2.3
C05/08	5mm	8mm	3.8
C05/09	5mm	9mm	5.5
C06/08	6mm	8mm	2.7
C06/09	6mm	9mm	4.4
C06/10	6mm	10mm	6.2
C06/11	6mm	11mm	8.3
C06/12	6mm	12mm	10.5
C07/10	7mm	10mm	5.0
C07/11	7mm	11mm	7.0
Coil length 50m			
C08/10	8mm	10mm	1.8
C08/11	8mm	11mm	2.8
C08/12	8mm	12mm	3.9
C08/14	8mm	14mm	6.4
C09/12	9mm	12mm	3.1
C09/13	9mm	13mm	4.3
C10/13	10mm	13mm	3.4
C10/14	10mm	14mm	4.7
C10/16	10mm	16mm	7.6
C12/15	12mm	15mm	3.9
C12/16	12mm	16mm	5.5
C12/17	12mm	17mm	7.1
C12/18	12mm	18mm	8.8
C12/19	12mm	19mm	10.6
C13/17	13mm	17mm	5.8
C13/19	13mm	19mm	9.3
C14/18	14mm	18mm	6.2
C14/20	14mm	20mm	9.9
C15/19	15mm	19mm	6.6
C15/20	15mm	20mm	8.5
C15/21	15mm	21mm	10.5
C15/23	15mm	23mm	14.8
C16/20	16mm	20mm	7.0
C16/21	16mm	21mm	9.0
C16/22	16mm	22mm	11.1
C18/22	18mm	22mm	7.8
C18/24	18mm	24mm	12.3
C19/24	19mm	24mm	10.5
C19/26	19mm	26mm	15.3
C19/27	19mm	27mm	17.9
C20/24	20mm	24mm	8.6
C20/26	20mm	26mm	13.4
C22/28	22mm	28mm	14.6
C24/30	24mm	30mm	15.8
Coil length 25m			
C25/31	25mm	31mm	8.2
C25/33	25mm	33mm	11.3
C25/35	25mm	35mm	14.6
C27/33	27mm	33mm	8.8
C30/37	30mm	37mm	11.4
C30/39	30mm	39mm	15.1
C30/40	30mm	40mm	17.0
C32/40	32mm	40mm	14.0
C32/42	32mm	42mm	18.0
C35/42	35mm	42mm	13.1
C35/45	35mm	45mm	19.5
C38/48	38mm	48mm	20.9
C40/48	40mm	48mm	17.1
C40/50	40mm	50mm	21.9
C45/55	45mm	55mm	24.3
C50/60	50mm	60mm	26.8

UK Standard Stock sizes in 30m coils.

Product Ref.	Size		Weight per coil kgs
	I.D.	O.D.	
C03/15	3mm	6mm	0.8
C05/15	5mm	8mm	1.1
C06/15	6mm	9mm	1.3
C08/15	8mm	11mm	1.7
C10/15	10mm	13mm	2.0
C12/15	12mm	15mm	2.4
C16/15	16mm	19mm	3.1
C04	4mm	10mm	2.4
C05	5mm	11mm	2.8
C06	6mm	12mm	3.2
C08	8mm	14mm	3.9
C10	10mm	16mm	4.6
C12	12mm	18mm	5.3
C16	16mm	22mm	6.7
C19	19mm	25mm	7.7
C22	22mm	28mm	8.8
C25	25mm	31mm	9.8
C32/5	32mm	42mm	21.6
C38/5	38mm	48mm	26.9
C44/5	44mm	54mm	28.6
C50/6	50mm	62mm	39.3

