

Get All You Need At Once

The horizontally designed BAR386 combines the benefits of a snooze alarm clock with weather display. Featuring animated icons to demonstrate clear, partially cloudy, cloudy and rainy, the BAR386 will help you keep track of the time as well as the changes in the weather 12 to 24 hours ahead. As with all the models in the One-Day range, the BAR386 is available in slick black and features an LCD display for clear viewing.

- Digital calendar and alarm clock with 8-minute snooze
- Weather forecast with animated icons
- Wireless thermometer
- Indoor / Outdoor temperature with trend indicator
- High / Low temperature alarms
- Moon phase
- Ice warning
- Comfort level indicator
- Battery life indicator
- LCD display
- Takes up to 3 remote sensors (1 included)
- Available in Matt black colour only.

Centralized weather information center
BAR386 Weather Station new range contains all necessary weather information around you. It includes the indoor / outdoor temperature, moon phase, temperature trends for your in-depth understanding of the weather. All information is shown on a clear LCD monitor at once.

Get alert to the weather change
The BAR386 Weather Station new range not just sits here for measuring the environmental change, but also keep you alert on the ice and temperature. You could set to sound if the sensor records above or below a temperature of your choice. Let you always be alerted on the weather change.

Main Unit

Dimensions	130L x 55W x 112H mm (5.1 x 2.1 x 4.4 in)
Weight	176g (6.2 oz) without batteries
Temperature unit	°C / °F
Temperature range	-5°C to 50°C (23°F to 122°F)
Resolution	0.1°C (0.2°F)
Clock frequency	DCF-77 (EU) / MSF-60 (UK)
Synchronization	Auto or disabled
Signal frequency	433 MHz
Clock	Auto or manual (disabled)
Memory	Min / Max relative temperature
Alarm duration	2 minutes
Snooze	8 minutes
Clock display	HH:MM:SS ; HH:MM:Day of Week
Hour format	12 / 24 hour format
Calendar	DD / MM language selectable: E, F, D, I, and S
Power	3 x UM-3 (AA) 1.5V batteries

Remote Unit

Dimensions	96L x 50W x 22H mm (3.8 x 2.0 x 0.9 in)
Weight	62g (2.22 oz) without battery
Transmission	

range	30m (100ft) unobstructed
Temperature range	-30°C to 60°C (-22°F to 140°F)
Power	1 x UM-3 (AA) 1.5V batteries

Note: We recommended that you use alkaline batteries with this product for longer usage and lithium batteries in temperatures below freezing.