



## DCS373N

### 18V XR Li-Ion Metal Cutting Circular Saw - Bare Unit

#### Selling Proposition

- XR Li-Ion premium Metal Cutting Circular Saw
- Part of the intelligent XR Lithium Ion Series designed for efficiency and making applications faster
- Powerful & highly efficient PM58 DEWALT fan-cooled motor with replaceable brushes delivers up to 3700 rotations per minute for fast cutting action
- Ergonomic handle set with rubber overmould to optimise end user comfort
- Extremely durable tool design with steel shoe to withstand rough job site conditions
- Intelligent trigger allowing total control over all applications

#### Standard Equipment

- 140 mm tungsten carbide blade
- Hex key
- Battery and charger sold separately

#### Warranty Specifications

- 3 year limited warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Battery chemistry	XR Li-Ion
Voltage	18 V
Blade Diameter	140 x 20 mm
Abgabeleistung	460 Watt
No Load Speed	3700 rpm
Max. Depth of Cut at 90°	43 mm
´Gewicht	3.1 kg
Länge	350 mm