

Junction box

Abox 350-L



Abox 350-L

Junction box

CUSTOMIZABLE

Productnumber: 83540001

Dimensions: 252 x 252 x 120 mm

Junction box, protection class IP55/IP66, nominal cross-section 35 mm², certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), DLG (Ammonia resistance), knockouts, M20/M25/M40/M50, (4 rear, 12 side), internal fixing points, for standard indoor and protected outdoor installations

grey, Ui=1000 V AC, without terminals

Accessories supplied:

4 attachment bushes IP55 M40 sealing range 17 - 30 mm, 1 sealing plug IP55 M40, cover retainer



Technical Data

electrical characteristics

Rated insulation voltage AC:	1000 V
Rated insulation voltage DC:	1000 V
Max. conductor cross section:	35 mm²
Protection class:	II
Type of protection:	IP55/IP66
Terminal type:	none

Colours

Base unit colour:	grey
Cover colour:	grey

Dimensions

Width:	252 mm
Length:	252 mm
Height:	120 mm
Inner length:	236 mm
Inner width:	236 mm
Inner height:	99 mm
Weight:	1.1834 kg

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	750 °C

mechanical properties

Impact strength:	IK07
Sealable:	yes

mechanical properties

Cover screw torque:	1.5 Nm
Type of fastening:	Wall/ceiling mounting
Fastening:	internal fixing points

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	55 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

Sales Information

EAN:	4013902660247
ETIM Class:	EC002600
Custom tariff number:	85389099
MOQ:	1

Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Thermoplastic elastomer
Cover screw material:	Stainless steel V2A

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
Test mark:	DLG (Ammonia resistance)

Accessories

[22742001 - KVR M20-MGM - Cable gland](#)

[22742101 - KVR M20-GDB/MGM - Cable gland](#)

[22744001 - KVR M40-MGM - Cable gland](#)

[22745001 - KVR M50-MGM - Cable gland](#)

[26042001 - DMS M20 - Double-membrane seals](#)

[26044001 - DMS M40 - Double-membrane seals](#)

[23042001 - AST M20 - Attachment bushes](#)

[23044001 - AST M40 - Attachment bushes](#)

[89513501 - Abox MPI 350 - Mounting plate](#)

[89533501 - Abox 250/350 NS35 - Standard rail](#)

[89600601 - Abox 100 KH 2006 6² - Terminal holder](#)

[89643501 - Abox 250/350 KLS-25²/35² - Terminal block](#)

[89604001 - MABF 215-1 - Mast/pipe fixing set](#)

Cable gland

