



ENGLISH

Datasheet

## RS Pro 3.5mm Pitch Straight PCB Terminal Block with Screw Termination, Through Hole, 3 Way

RS Stock No: **790-1143**



### Product Details

RS Pro 3.5 mm pitch straight PCB terminal block is suitable for 16-26 AWG wire. This 3-way professional range PCB terminal block features screw termination method. The PCB terminal block with through hole has rectangular Tin plated PC tails which is 0.9 x 0.5 mm by 3.5 mm long.

**Specifications:**

Body Orientation	Straight
Colour	Green
Current Rating	10 A
Depth	8.5 mm
Gender	Female
Length	10.5 mm
Material	Nylon 66
Mounting Type	Through Hole
Number of Contacts	3
Number of Rows	1
Pitch	3.5 mm
Termination Method	Screw
Type	PCB Terminal Block
Voltage Rating	300 V
Width	7.2 mm
Insulation Resistance	>2000 mΩ
American Wire Gauge	16 to 26 AWG
Insulation Withstand Voltage	2000 V ac
Operating Temperature Range	-40 to +105°C
Flammability Rating	UL 94 V-0