







Process Connections for Thermostats (606710)

- Protection tubes
- Screw connections
- Adapter set for protection tube
- Adapter set for DIN-rail mounting
- Holder for probe line JUMO frostTHERM-AT
- Sheet flange
- Wall mount



Order details

(1) Basic type		
606710	Pockets	
(2) Process connection		
20	Screw-in thermowell	
23	Pocket + welding collar, conical	
28	Pocket for heatTHERM, 1 probe	
29	Pocket for heatTHERM, 2 probes	
42	Weld-in pocket with union nut, conical	
49	Protection tube heatTHERM, 2 probes, Ø 15 mm	
60	Double screw connection standard	
65	Screw fitting with sealing gland	
70	Strap 15 - 100 mm	
72	Metal flange	
73	Wall bracket	
75	Adapter for ATH-pocket	
78	Bracket capillary 3 pieces	
79	Bracket capillary 6 pieces	
90	Mounting kit f. mount. rail heatTHERM/EM	
(3) Thread		
00	Without thread	
12	G 3/8	
13	G 1/2	
14	G 3/4	
35	M14x1	
(4) Process connection material		
00	Without process connection	
20	CrNi (stainless steel)	
46	CuZn (brass)	
(5) Fitting length		

000	Without pocket
100	100 mm
120	120 mm
150	150 mm
200	200 mm
250	250 mm
300	300 mm
350	350 mm
400	400 mm
450	450 mm
500	500 mm
(6) Immersion tube diameter	
00	Without thermowell
10	10 mm
15	15 mm
8	8 mm
(7) Extra codes	
000	Without extra code
643	Clamp with short and long screw

Order code

(1) (2) (3) (4) (5) (6) (7)
 / - - - - /

For orders < EUR 100 a processing fee of EUR 25 applies.



Stock versions

Order code	Process connection	Thread	Process connection material	Fitting length	Immersion tube diameter	Part no.
606710/75-00-01-000-00/000	Adapter for ATH-pocket	Without thread	Steel	Without pocket	Without thermowell	00507273
606710/90-00-00-000-00/000	Mounting kit f. mount. rail heatT-HERM/EM	Without thread	Without process connection	Without pocket	Without thermowell	00511794
606710/79-00-00-000-00/000	Bracket capillary 6 pieces	Without thread	Without process connection	Without pocket	Without thermowell	00558730
606710/78-00-00-000-00/000	Bracket capillary 3 pieces	Without thread	Without process connection	Without pocket	Without thermowell	00558731
606710/72-00-00-000-00/000	Metal flange	Without thread	Without process connection	Without pocket	Without thermowell	60677200
606710/73-00-00-000-00/000	Wall bracket	Without thread	Without process connection	Without pocket	Without thermowell	60171300
606710/20-13-46-100-8/000	Screw-in thermowell	G 1/2	CuZn (brass)	100 mm	8 mm	60694004
606710/20-13-46-120-8/000	Screw-in thermowell	G 1/2	CuZn (brass)	120 mm	8 mm	60694017
606710/20-13-46-150-8/000	Screw-in thermowell	G 1/2	CuZn (brass)	150 mm	8 mm	60694007
606710/20-13-46-200-8/000	Screw-in thermowell	G 1/2	CuZn (brass)	200 mm	8 mm	60694010
606710/20-13-46-300-8/000	Screw-in thermowell	G 1/2	CuZn (brass)	300 mm	8 mm	60694013
606710/20-13-46-100-15/000	Screw-in thermowell	G 1/2	CuZn (brass)	100 mm	15 mm	60695003
606710/20-13-46-120-15/000	Screw-in thermowell	G 1/2	CuZn (brass)	120 mm	15 mm	60696011
606710/20-13-46-150-15/000	Screw-in thermowell	G 1/2	CuZn (brass)	150 mm	15 mm	60696001
606710/20-13-46-200-15/000	Screw-in thermowell	G 1/2	CuZn (brass)	200 mm	15 mm	60696002
606710/20-13-46-300-15/000	Screw-in thermowell	G 1/2	CuZn (brass)	300 mm	15 mm	60696003
606710/20-13-20-100-8/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	100 mm	8 mm	60694006
606710/20-13-20-120-8/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	120 mm	8 mm	60694050
606710/20-13-20-150-8/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	150 mm	8 mm	60694009
606710/20-13-20-200-8/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	200 mm	8 mm	60694012
606710/20-13-20-300-8/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	300 mm	8 mm	60694015
606710/20-13-20-100-15/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	100 mm	15 mm	60695002
606710/20-13-20-120-15/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	120 mm	15 mm	60694028
606710/20-13-20-150-15/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	150 mm	15 mm	60696013
606710/20-13-20-200-15/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	200 mm	15 mm	60696023
606710/20-13-20-300-15/000	Screw-in thermowell	G 1/2	CrNi (stainless steel)	300 mm	15 mm	60696033
606710/42-14-01-170-8/000	Weld-in pocket with union nut, conical	G 3/4	Steel	170 mm	8 mm	60694003
606710/42-14-01-200-8/000	Weld-in pocket with union nut, conical	G 3/4	Steel	200 mm	8 mm	60694002
606710/60-12-46-000-00/000	Double screw connection standard	G 3/8	CuZn (brass)	Without pocket	Without thermowell	60450000
606710/60-13-46-000-00/000	Double screw connection standard	G 1/2	CuZn (brass)	Without pocket	Without thermowell	60453000
606710/60-12-20-000-00/000	Double screw connection standard	G 3/8	CrNi (stainless steel)	Without pocket	Without thermowell	60452000
606710/60-13-20-000-00/000	Double screw connection standard	G 1/2	CrNi (stainless steel)	Without pocket	Without thermowell	60456000

606710/65-35-46-000-00/000	Screw fitting with sealing gland	M14x1	CuZn (brass)	Without pocket	Without thermo-well	60434005
606710/65-35-20-000-00/000	Screw fitting with sealing gland	M14x1	CrNi (stainless steel)	Without pocket	Without thermo-well	60434006
606710/28-13-46-100-8/000	Pocket for heatTHERM, 1 probe	G 1/2	CuZn (brass)	100 mm	8 mm	60003177
606710/28-13-46-150-8/000	Pocket for heatTHERM, 1 probe	G 1/2	CuZn (brass)	150 mm	8 mm	60003203
606710/28-13-46-200-8/000	Pocket for heatTHERM, 1 probe	G 1/2	CuZn (brass)	200 mm	8 mm	60003171
606710/28-13-20-100-8/000	Pocket for heatTHERM, 1 probe	G 1/2	CrNi (stainless steel)	100 mm	8 mm	60003172
606710/28-13-20-150-8/000	Pocket for heatTHERM, 1 probe	G 1/2	CrNi (stainless steel)	150 mm	8 mm	60003205
606710/28-13-20-200-8/000	Pocket for heatTHERM, 1 probe	G 1/2	CrNi (stainless steel)	200 mm	8 mm	60003173
606710/29-13-46-100-8/000	Pocket for heatTHERM, 2 probes	G 1/2	CuZn (brass)	100 mm	8 mm	60003178
606710/29-13-46-150-8/000	Pocket for heatTHERM, 2 probes	G 1/2	CuZn (brass)	150 mm	8 mm	60003204
606710/29-13-46-200-8/000	Pocket for heatTHERM, 2 probes	G 1/2	CuZn (brass)	200 mm	8 mm	60003174
606710/49-13-20-100-15/000	Protection tube heatTHERM, 2 probes, Ø 15 mm	G 1/2	CrNi (stainless steel)	100 mm	15 mm	60003175
606710/49-13-20-150-15/000	Protection tube heatTHERM, 2 probes, Ø 15 mm	G 1/2	CrNi (stainless steel)	150 mm	15 mm	60003206
606710/49-13-20-200-15/000	Protection tube heatTHERM, 2 probes, Ø 15 mm	G 1/2	CrNi (stainless steel)	200 mm	15 mm	60003176