

Endress+Hauser TMT84-A1A1A

iTEMP TMT84, Transmitter PA



Picture for reference only. Product appearance may vary based on configuration

Dual sensor input. Advanced diagnostics: sensor monitoring. PROFIBUS PA Profile 3.02.

Configuration of TMT84-A1A1A:

Approval:	A1	Non-hazardous area
Output Signal:	A	PROFIBUS PA
Electrical Connection:	1	Push-in terminals, housing form B, DIN EN 50446
Field Housing:	A	W/o, mounting set DIN terminal head

Alternative part number: TMT84-1082/0