




All MQS, CONNECTOR HOUSING (199)

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 936123-1 MQS 4P DBL HSG	 TE Part # CAT-N01-AT063064 0.63 mm to 0.64 mm Automation Ready Terminals for Advanced Automotive Wire Harness Assembly Automation	 TE Part # 4-1579007-8 EXTRACTION TOOL	 TE Part # CAT-N02-MUC063 MQS 0.63mm Unsealed Connector System
 TE Part # 936120-2 MQS 4P PLUG HSG YELLOW	 TE Part # CAT-SIGH262 Signal Header	 TE Part # 936121-2 MQS 4P CAP ASSY YELLOW	

Customers Also Bought

 TE Part #936121-1 4POS MQS TAB	 TE Part #CAT-N01-AT063064 0.63 mm to 0.64 mm Automation Ready Terminals for Advanced Automotive Wire Harness Assembly Automation	 TE Part #4-1904124-3 V23074A1001A403-EV-CBOX	 TE Part #2109006-3 060 REC(M) CONT
 TE Part #5-2219072-2 ABS 46P COVER ASSY TYPE A NON- CPA	 TE Part #2219195-2 COVER HSG FOR ECU 68P PLUG PF	 TE Part #5-2296315-5 ACU 52P PLUG ASSY(B5B8)	 TE Part #CAT-T4827-CH8172 Timer Connector Housing

Documents

Product Drawings

MQS 4P PLUG ASSY YELLOW

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_936119-2_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_936119-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_936119-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English