

FW95 - Steel PVC Wellington S5 FO

Collection: Portwest™ Work

Range: Foot Protection

Material Upper: PVC/Nitrile

Material Outsole: PVC/Nitrile

Outer Carton: 10

Product information

The Total Safety Wellington offers ultimate S5 protection to the wearer. Steel toecap and midsole. PVC/Nitrile construction that is waterproof and resistant to oil, fuels and acids. Suitable for a variety of environments.

Portwest™ Work

Complete range of styles made of polymeric materials. Durable and waterproof construction that is highly resistant to fuels, oils, grease and fats.

Foot Protection

Innovation, design, styling and quality components define the Portwest foot protection collection.

Standards

EN ISO 20345:2022 S5

EN 13832-3: 2018



Features

- Kick spur
- Reinforced ankle protection
- Fully waterproof
- Dual density PVC/Nitrile construction
- Chemical resistant
- Protective steel toecap
- Pierce resistant steel midsole
- Anti-static footwear
- Energy absorbing seat region
- 100% Waterproof to keep feet dry
- Fuel and oil resistant outsole



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

FW95 - Steel PVC Wellington S5 FO

Commodity Code: 6401100000

Test House

Intertek Italia S.p.A. (Notified Body No.: NB: 2575)

Via Guido Miglioli 2/A,

-, Italy

Cert No: ITASLNB23024644

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FW95WHR36	White	44.0	44.0	44.0	1.9000	0.0852	5036108251902	25036108740639
FW95WHR37	White	44.0	44.0	44.0	1.8800	0.0852	5036108251919	25036108740646
FW95WHR38	White	44.0	44.0	44.0	1.7800	0.0852	5036108251926	25036108740653
FW95WHR39	White	44.0	44.0	44.0	2.0300	0.0852	5036108251933	25036108740660
FW95WHR40	White	44.0	44.0	44.0	2.0300	0.0852	5036108251940	25036108740677
FW95WHR41	White	44.0	44.0	44.0	2.3200	0.0852	5036108251957	25036108740684
FW95WHR42	White	44.0	44.0	44.0	2.2800	0.0852	5036108251964	25036108740691
FW95WHR43	White	44.0	44.0	44.0	2.3200	0.0852	5036108251971	25036108740707
FW95WHR44	White	44.0	44.0	44.0	2.5200	0.0852	5036108251988	25036108740714
FW95WHR45	White	44.0	44.0	44.0	2.5500	0.0852	5036108251995	25036108740721
FW95WHR46	White	44.0	44.0	44.0	2.7900	0.0852	5036108252008	25036108740738
FW95WHR47	White	44.0	44.0	44.0	2.6500	0.0852	5036108252015	25036108740745
FW95WHR48	White	44.0	44.0	44.0	2.6400	0.0852	5036108252022	25036108740752