

The Yale logo, consisting of the word "Yale" in a bold, black, sans-serif font, centered within a bright yellow circle.

Brass Padlocks

With 180 years of manufacturing expertise, an exclusive Yale design and rigorous testing, the Yale Brass Padlocks have been built with you in mind. Suitable for your gym locker, securing your DIY tools in your tool box or any belonging you want to keep safe and secure indoors. Our padlocks come in 10 different sizes with 3 keys and are available in standard and long shackle length to suit your needs. Yale takes care of your possessions; you take care of the rest.

Suitable for



Indoors



Lockers



Tool box



Rucksack

Features

- Multi packs available in 15mm/20mm/25mm/ 30mm/35mm & 40mm Brass Padlock with keyed alike for convenience
- 30mm and above padlocks tested to EN12320:2012, stimulating forms of attack such as cutting, pulling and twisting of the shackle
- Tested between 48 and 240 hours for corrosion resistance to ensure protection against different weather conditions
- Sizes 30mm and above padlocks are tested to 10,000 cycles (opening and closing) for optimum performance
- Available in standard and long shackle lengths for various applications
- 10% footprint reduction on Yale padlock packaging



Trusted every day



Description	Brass Padlock 15mm	Brass Padlock 20mm	Brass Padlock 25mm	Brass Padlock 30mm	Brass Padlock 35mm
Padlock Part no.	Y110JB/15/111/4	Y110B/20/111/1	Y110B/25/113/1	Y110B/30/115/1	Y110B/35/120/1
Locking points	Single locking	Single locking	Single locking	Double locking	Double locking
Body material	Brass	Brass	Brass	Brass	Brass
Shackle material	Steel	Steel	Steel	Hardened steel	Hardened steel
Vertical shackle clearance	14.5mm	23.5mm	13mm	17mm	20.5mm
Horizontal shackle clearance	8.2mm	10.8mm	14mm	15mm	19mm
Weight with keys	75g	45g	65g	90g	115g
Dimensions	W: 20 H: 19 D: 13.3 Ø: 2.8	W: 21.4 H: 21.8 D: 10 Ø: 3.3	W: 25 H: 25.5 D: 11 Ø: 4.2	W: 30 H: 28.3 D: 13 Ø: 5	W: 35 H: 31 D: 14 Ø: 5.5
Corrosion resistance	48 hours	48 hours	48 hours	96 hours	96 hours
Keys	3 keys	3 keys	3 keys	3 keys	3 keys
Pins	3 pin cylinder	3 pin cylinder	4 pin cylinder	4 pin cylinder	4 pin cylinder



Description	Brass Padlock Long Shackle 20mm	Brass Padlock Long Shackle 25mm	Brass Padlock Long Shackle 30mm	Brass Padlock Long Shackle 40mm	Brass Padlock Long Shackle 50mm
Padlock Part no.	Y110B/20/122/1	Y110B/25/125/1	Y110B/30/132/1	Y110B/40/140/1	Y110B/50/166/1
Locking points	Single locking	Single locking	Double Locking Brass Latch	Double Locking Brass Latch	Double Locking Brass Latch
Body material	Brass	Brass	Brass	Brass	Brass
Shackle material	Steel	Steel	Hardened steel	Hardened steel	Hardened steel
Vertical shackle clearance	23.5mm	25mm	33mm	40mm	58mm
Horizontal shackle clearance	10.8mm	14mm	15mm	22mm	29.5mm
Weight with keys	45g	65g	90g	170g	300g
Dimensions	W: 21.4 H: 21.8 D: 10 Ø: 3.3	W: 25 H: 26 D: 11 Ø: 4	W: 30 H: 28.3 D: 13 Ø: 5	W: 40 H: 35 D: 14 Ø: 6	W: 50 H: 40.7 D: 17 Ø: 8
Corrosion resistance	48 hours	48 hours	96 hours	96 hours	96 hours
Keys	3 keys	3 keys	3 keys	3 keys	3 keys
Pins	3 pin cylinder	4 pin cylinder	4 pin cylinder	5 pin cylinder	5 pin cylinder
CEN rating	-	-	1	1	2



Description	Brass Padlock 40mm	Brass Padlock 50mm	Brass Padlock 50mm Adjustable Shackle pk 1	Brass Padlock 60mm	Brass Padlock 70mm
Padlock Part no.	Y110B/40/122/1	Y110B/50/126/1	Y110B/50/155/1	Y110B/60/132/1	Y110B/70/137/1
Locking points	Double locking	Double locking	Double Locking Brass Latch	Double locking	Double locking
Body material	Brass	Brass	Brass	Brass	Brass
Shackle material	Hardened steel	Hardened steel	Hardened steel	Hardened steel	Hardened steel
Vertical shackle clearance	22mm	29.5mm	58.1 - 152.6mm	31mm	41mm
Horizontal shackle clearance	22mm	27.5mm	27.5mm	32mm	37mm
Weight with keys	275g	300g	375g	425g	610g
Dimensions	W: 40 H: 34.8 D: 14 Ø: 6.3	W: 50 H: 40.7 D: 17 Ø: 8	W: 50 H: 17 D: 42.2 Ø: 8	W: 60 H: 47.1 D: 18 Ø: 10	W: 70 H: 54.1 D: 20 Ø: 11
Corrosion resistance	96 hours	96 hours	240 hours	96 hours	96 hours
Keys	3 keys	3 keys	3 keys	3 keys	3 keys
Pins	5 pin cylinder	5 pin cylinder	5 pin cylinder	5 pin cylinder	5 pin cylinder
CEN rating	1	2	2	2	2