

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2124150400](#)  
**Status:** **Active**  
**Overview:** [Board-in Connectors](#)  
**Description:** 2.50mm Pitch, Board-In Crimp Housing, 4 Circuits, Right-Angle, Natural

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification 2124150000PK-000 \(PDF\)](#)  
[Product Specification 2124150000PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">212415</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">Board-in Connectors</a>
Product Name	Board-in
UPC	193264513659

**Physical**

Circuits (maximum)	4
Color - Resin	Natural
Gender	N/A
Glow-Wire Capable	No
Material - Resin	Polyamide
Net Weight	0.113/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Crimp Specification	350210000CS-000
Packaging Specification	2124150000PK-000
Product Specification	2124150000PS-000
Sales Drawing	2124150000-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[212415 Series](#)

**Mates With**

2.50mm Pitch Board-In Crimp Terminal  
[350211001](#) , [350211160](#)