

ITEM # ATS22D88S6, SOFT START

Soft Start



Specifications

Family	Altistart 22
Product Line	Soft Starters
Application	Constant & Variable Torque
Enclosure Rating	IP20 (IP00 if no connections)
Frame Size	B
Output Ampere Rating	88
Maximum HP Rating 208V	25
Maximum HP Rating 230V	30
Maximum kW Rating 400V	37
Maximum HP Rating 460V	60
Maximum HP Rating 575V	75
Control Voltage	220 Vac (-15% to + 10%)
Logic Input	3
Analog Input	1 PTC probe

Analog Output	N/A
Logic/Relay Outputs	2 (N/C / NO)
Communication	Modbus
Weight [lb]	17.20
Weight [kg]	7.80
UL File No.	E184727
CSA File	224330
Other	UL, CSA,CE,GOST,C-Tick,CCC and RoHS