

AMP **AMP Connect**

Alphabetical SEARCH	Picture SEARCH	Part Number SEARCH
----------------------------	-----------------------	---------------------------

[Go To Step Search™ Screen](#)

719553-1 -- 1 of 1 products

Terminals and Splices

AMPOWER II and III/AMPOWER R Terminals and Splices

General **INFO**

Sales **INFO**



Line art represents typical product only.

 [Line Art](#)

Searchable Features:

Product Type	Terminal
Product Series	AMPOWER III
# of Holes	1
Wire Size	[35.00 ²] AWG [mm]
Stud Size	6

Other Properties:

Dim. C	.276 [7.00] in. [mm]
Dim. D	.354 [9.00] in. [mm]
Dim. L	1.496 [38.00] in. [mm]
Dim. W	.669 [17.00] in. [mm]
Material	Copper
Plating	Tin
Stud Hole Diameter	.252 [6.40]
Hydraulic Hand Tool	SIMABLOC 45, SIMABLOC U 12
Hydraulic Head	HEAD V 13 U NG, HEAD V 20 U NG, Reducer 2S1
Electro-Hydraulic Hand Tool	AUTOPRESS 55
Mechanical Hand Tool	ISOLEC III
AMPOWER III Dies	13M+13P AMP III