

D25134KP-QS

SDS-plus 800W 2.8J Rotary Hammer

5035048640111



Product Description:

Impact Force (E.P.T.A.): 2.8JR No-load Load (rpm): 0-1500Ø Wood/Concrete/Metal/Drill Bit (mm): 30/26/13/65Stroke Rate (cps/min): 0- 5540Vibration Level (m/s²): 15.7Mode (Rotation/Perforation/Impact): 3Quick-Change Chuck

Product features and benefits:

- Ideal for drilling anchor holes in concrete from 4 to 22 mm Diameter chuck Quick change, use your 3 jaw chuck to drill
- Rounded shapes offering a better fit, more comfortable, in
- All applications Rotation stop for light chiseling in soft building materials, brick and occasionally concrete
-
- Lightweight ventilation slots arranged so that air is not blown into the
- Electronically variable speed allows for easy control of the tool
- Reinforced sealing to have optimal protection of the mechanism against dust and ensuring a better longevity
- Rubber-coated rear handle for comfort
- Striking stop for simple rotary drilling in wood, metal, tiles
-

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Depth stop (x1)
- Quick Change Chuck 13 mm (x1)
- Box (x1)

Specifications techniques :

- - Drilling capacity (wood):
30 mm
 - Power: 800 W
 - Power supply: 800 W
- Drilling Capacity (Metal):

13 mm

D25134KP-QS

SDS-plus 800W 2.8J Rotary Hammer

5035048640111

Product in the D25134KP-QS composition

Ref	▲ ▼ Title	▲ ▼
10mm (x2)		
D25134K-QS	SDS-plus 800W 2.8J Rotary Hammer	
DT60302-QZ	Pack of 6 SDS-Plus Drill Bits Ø	
DT60330-QZ	Pack of two flat chisels 250x20mm and 250x40mm and a 250mm SDS-Plus tip	
MP17225-QZ	TSTAK STICKERS FOR D25134KP	