



PRODUCT-DETAILS

SPUL25/25M

25MM GS-PVC COAT CONDUIT 25M - GR



General Information

Extended Product Type:	SPUL25/25M
Product ID:	7TCA296030R0368
EAN:	5020963006616
Catalog Description:	25MM GS-PVC COAT CONDUIT 25M - GR
Long Description:	Liquid Tight, Medium Flexibility, Covered Steel Conduit, 3/4 Inch, Nominal Conduit Size 25mm, Outside Diameter 26.4mm, Inside Diameter 21.0mm, Static Bend Radius 105mm, Reel Length 25 Meters, UL Listed and CSA Approved, PVC Covered Galvanised Steel Core with Copper Packing, Grey
Display Name:	SPUL25/25M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Flexible Protection Systems

Ordering

EAN: 5020963006616

UPC: 786210247571

Dimensions

Outside Diameter: 26.4 mm

Technical

Number of Batteries: 0

Color: Gray

Material: Galvanized Steel Core with PVC Cover and Copper Packing

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963006616

Package Level 1 Height: 11.4 in
290 mm

Package Level 1 Depth / Length: 19.29 in
490 mm

Package Level 1 Width: 19.29 in
490 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

