

FUBW50020

Secvest wireless outdoor motion detector

Due to its wireless technology, the passive infrared motion detector with dual PIR element enables easy and wireless installation outdoors. The detector reacts to all types of body heat and reports this to an alarm panel or video surveillance system.

The integrated PIR elements can be panned 180° and tilted 90°, meaning the detector can be installed in virtually any location. Installation positions opposite sources of heat are not suitable. Do not install the motion detector near electric cables, gas lines or electronic equipment that generates heat during long periods of operation.

The angle of view of the outdoor motion sensor is 10°–70°, and its detection range – depending on installation height – is up to 30 meters.



Product highlights:

- Flexible and easy installation due to the newest wireless technology
 - Suitable for alarm and video surveillance systems
 - Dual PIR element
 - Detection range up to 30 m
 - Protection class IP55
-

FUBW50020

Secvest wireless outdoor motion detector

Technical Data

Dimensions (WxHxD)	155x120x115
Detection	Heat detection
Housing material	Polyethylene HDPE
Max. battery life	2 years
Modulation	FM
Range	free field: 100m, indoors: 30m
Tamper monitoring	yes
Sensor type	Independent duplex PIR unit
Power supply	230 VAC, 9–15 VDC
Voltage monitoring	yes
Status display	LED
Environmental class	III