

Tool caulk gun cartridge



Technical characteristics

Max operating pressure: 6,2 bar

Connection: Supplied with 3 adaptors: ISO 6150 B; European 7,4 mm; ARO 210

	A (mm)	B (mm)	Operating pressure (bar)	Dimensions (tube (mm))	Capacity (Cartridge - ml)	Air consumption (l/min)	BSPT female thread	Weight (kg)	Parts Numbers
	311	165	4.8	50 x 210	310	113	R 1/4	1.1	TCG C300

