
# KERN **BID 1T-4SM**

Floor scale with the best price-to-performance ratio, verification optional



## Category

| | |
|---|---|
| Brand | KERN |
| Product category | Industrial scale |
| Product group | Floor scale |
| Product family | BID |

## Measuring System

| | |
|---|---|
| Weighing system | Strain gauge |
| Number of weighing ranges | 1 |
| Weighing capacity [Max] | 1500 kg |
| Readability [d] | 0,5 kg |
| Reproducibility | 0,5 kg |
| Linearity | ± 1,5 kg |
| Minimum weight [Min] (verifiable) | 10 kg |
| Resolution | 3.000 |
| Tare range | 1500 kg |
| Adjustment options | Adjusting with external weight |
| Recommended adjusting weight | 1500 kg (M2) |
| Stabilization time | 2 s |
| Linearisation in dots | 3 |
| Eccentric loading at 1/3 [Max] | 2,5 kg |
| Conformity assessment possible | ✓ |
| Construction type of the scale | Single-range balance |
| Units | kg<br>g<br>lb<br>oz<br>PCS<br>tJ<br>HJ |
| Units (if device is conformity assessed) | kg |
| Load cell connection | 4-wire |
| Default unit | kg |
| Loadcell type | KELI SQB |

## Display

| | |
|---|---|
| Display type | LCD |
| Display type | LCD |
| Display backlight | ✓ |
| Display screen size | 110×35 mm |
| Display segments | 6 |
| Display digit height - smallest digit | 25 mm |
| Display digit height | 25 mm |
| Languages of the user interface | Symbol language |

## Construction

| | |
|---|---|
| Dimension (W×D×H) | 1200×1000×108 mm |
| Dimension display device (W×D×H) | 268×115×80 mm |
| Dimensions weighing surface (W×D) | 1000×1000 mm |
| Dimensions weighing surface | 1000×1000 mm |
| Dimensions weighing platform (W×D×H) | 1000×1000×108 mm |
| Material | steel, lacquered |
| Material weighing plate | steel, powder-coated |
| Material platform | steel, powder-coated |
| Material display housing | plastic |
| Material load cell(s) | steel |
| Material substructure | steel, powder-coated |
| Level indicator | ✓ |
| Levelling feet adjustable | ✓ |
| Wall mount | ✓ |
| Cable length | 5 m |
| Display device cable length | 5 m |
| Allowed cable length display device [Max] | 15 m |
| Platform Construction | Chequer plate, welded |
| Load cells - number | 4 |

## Functions

| | |
|---|---|
| PreTare function | ✓ |
| Recipe/summing level | Sum A |
| Percentage determination | ✓ |
| Tolerance weighing | ✓ |
| Tolerance weighing - type of signal | acoustically<br>visual |
| Underfloor weighing | None |
| Alibi memory | optional internal memory |
| Alibi memory - number of memory spaces | 250.000 |

# KERN **BID 1T-4SM**

Floor scale with the best price-to-performance ratio, verification optional

| | |
|---|---|
| Function for averaging under unstable weighing conditions | ✓ |
| Counting function | ✓ |
| IP protection - complete device | IP65 |
| IP protection - display | IP65 |
| IP protection - platform | IP67 |
| IP protection - load cell | IP67 |
| Auto-off interval(s) in battery mode/rechargeable battery mode | 3 min<br>off<br>5 min<br>30 min<br>15 min |
| Auto-off interval(s) in mains power mode | 3 min<br>off<br>5 min<br>30 min<br>15 min |
| Tare function | manual (multi) |
| Number of keys for operation | 7 |

## Interface

| | |
|---|---|
| Interfaces | RS-232 standard<br>Ethernet (optional, factory)<br>USB (optional, factory)<br>WiFi (optional, factory)<br>Alibi memory (optional, factory)<br>USB-Host/Master (optional, factory) |

## Power Supply

| | |
|---|---|
| Supplied power supply | Power supply unit |
| Power supply type | Power adapter |
| Plug-in power supply / adapter for countries - included with the delivery | EURO<br>UK<br>US<br>CH |
| Plug-in power supply / adapter for countries - optional | EURO<br>UK<br>US |
| Input voltage power supply / power [Max] | 100 V - 240 V AC 50/60 Hz 0.4 A max |
| Power supply cable removable | removable |
| Input voltage device / power [Max] | 12 V DC, 1000 mA |
| Power socket for mains adapter | Inside plus, outside minus |
| Battery / accumulator type | Pb |
| Battery | no battery |
| Rechargeable battery | 6 V; 1.3 Ah |
| Rechargeable battery operating time - backlight on | 26 h |
| Rechargeable battery operating time - backlight off | 43 h |
| Rechargeable battery charging time | 3 h |
| Rechargeable battery optional | Rchrg. battery optional - intern |
| Battery/Accu connected | fixed electrical connection, not insulated |

## Environmental conditions

| | |
|---|---|
| Ambient temperature [Min] | -10 °C |
| Ambient temperature [Max] | 40 °C |
| Humity of environment [Min] | 0 % |
| Humity of environment [Max] | 80 % |

## Approval

| | |
|---|---|
| CE mark | ✓ |
| Conformity assessment possible ex works | ✓ |
| Accuracy classe | III |
| Verification scale interval [e] | 0,5 kg |

## Services (optional)

| | |
|---|---|
| Article number for adjustment at the location of installation | 961-250 |
| Article number for conformity assessment | 965-230 |
| Article number for DAkkS calibration | 963-130 |
| Article number for certificate of conformity | 969-517 |

## Packing & Shipping

| | |
|---|---|
| Delivery time | 2 d |
| Dimensions packaging (W×D×H) | 1050×1050×260 mm |
| Shipping method | Freight |
| Net weight approx. | 70 kg |
| Gross weight approx. | 95 kg |
| Shipping weight | 95 kg |

## Product information


| | |
|---|---|
| GTIN/EAN number | 4045761207134 |
| Trade number | 84238220 |
| REACH classification | no prohibited substances |

# KERN **BID 1T-4SM**

Floor scale with the best price-to-performance ratio, verification optional

## Pictograms

### STANDARD




### OPTION




### FACTORY

