

## General Information

Extended Product Type:	316ERU6W
Product ID:	2CMA101296R1000
EAN:	7392696012966
Catalog Description:	Panel mounted socket outlets, 3P+E, 16A, 380 ... 415 V
Long Description:	Panel mounted socket outlets, 3P+E, 16A, 380 ... 415 V

## Additional Information

Additional Information:	3P+E
Cable Cross-Section:	1 ... 2.5 mm <sup>2</sup>
Color:	Red
Connection Type:	Screw clamp
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700006C0201
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	IP67
E-nummer:	2417691
EAC Certificate:	RU C-CZ.ME77.B.02742
EAN:	7392696012966
ETIM 5:	EC001321 - CEE socket outlet
ETIM 6:	EC001317 - Panel-mounted CEE socket outlet
Enclosure Material:	Plastic (PA)
Environmental Information:	2CMC700001D0002
Frequency (f):	50 Hz 60 Hz
Function:	Socket outlet for panel mounting
Gross Weight:	0.18 kg
Housing Material:	Plastic (PA)
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#316ERU6W
Minimum Order Quantity:	10 piece
Number of Poles:	4
Package Level 1 EAN:	7392696021531
Package Level 1 Gross Weight:	1.8 kg
Package Level 1 Height:	442 mm
Package Level 1 Length:	187 mm
Package Level 1 Units:	10 piece
Package Level 1 Width:	74 mm
Product Main Type:	ERU
Product Name:	Panel mounted socket outlet
Product Net Depth:	84 mm
Product Net Height:	98 mm
Product Net Length:	84 mm
Product Net Weight:	0.18 kg

Product Net Width:	85 mm
Protection Type:	Watertight
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	380 ... 415 V
SEMKO Certificate:	1616293
Selling Unit of Measure:	piece
Short Description:	Panel mounted socket outlets, 3P+E, 16A, 380 ... 415 V
Size:	88x85x98
Standards:	IEC 60309-1 IEC 60309-2
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour
RAL Number:	RAL 7012 - Basalt Grey