

ZB 8/WH-100:UNBEDRUCKT - Zack marker strip



5060896

<https://www.phoenixcontact.com/gb/products/5060896>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 8.2 mm, Number of individual labels: 1000, text field height: 10.5 mm, text field width: 8.15 mm

Your advantages

- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

Commercial data

Item number	5060896
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG2112
Product key	BG2112
Catalog page	Page 120 (C-3-2019)
GTIN	4017918096120
Weight per piece (including packing)	1.8 g
Weight per piece (excluding packing)	1.8 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Terminal marking
Pitch	8.2 mm
Type	high

Marking

Number of individual labels	1000
Number of individual labels per row	10
Number of marker strips	100

Dimensions

Width	8 mm
Pitch	8.2 mm

Text field

Text field width	8.15 mm
Text field height	10.5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

ZB 8/WH-100:UNBEDRUCKT - Zack marker strip



5060896

<https://www.phoenixcontact.com/gb/products/5060896>

Mounting

Mounting type	latching
---------------	----------

Drawings

Schematic diagram



ZB 8/WH-100:UNBEDRUCKT - Zack marker strip



5060896

<https://www.phoenixcontact.com/gb/products/5060896>

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 8/WH-100:UNBEDRUCKT - Zack marker strip



5060896

<https://www.phoenixcontact.com/gb/products/5060896>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.015 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk