

# ESD SMD tweezers set 6 pcs

<b>Art.-No.</b>	5-060
<b>Description</b>	ESD SMD tweezers set 6 pcs
<b>Application</b>	Electronics, placement tweezers, SMD/THT precision tweezers
<b>Specification</b>	Dimensions see data sheets individual articles (pictogram)
<b>Material</b>	stainless steel
<b>Surface/Coating</b>	matt finish
<b>Features</b>	stainless, antimagnetic, acid-resistant, dissipative
<b>Surface resistance</b>	/
<b>Total length</b>	measures 130 × 140 × 20 mm
<b>Weight</b>	weight 155 g

## Application and technical data

Tweezers for SMD/THT technology, for gripping parts and components such as mini MELFs, diodes, resistors or precise pick-up of filigree wires.

100% stainless steel anti-magnetic, rustproof and acid-resistant, reflection-free matt fine polished. Stainless austenitic chromium nickel quality steel with low carbon content, for good corrosion resistance (not seawater resistant).

Case consisting of ESD imitation leather, EPA suitable for electrostatically protected areas (ESD workplace/ESD protection zone corresponds to standard DIN EN 61340-5-1), dissipative 10^6 Ohm. The leatherette is flame retardant, biocompatible and contains a dissipative Velcro strap to prevent static charge when opening.

## Parts list

ESD SMD tweezers set consists of:

- 5-060-0-ESD ESD dissipative leatherette bag 6 empty pockets
- 5-049-13 ESD SMD tweezers 110 mm form 4 stainless steel dissipative
- 5-055-13 ESD SMD tweezers 120 mm form 7a stainless steel angle 40° dissipative
- 5-059-13 ESD SMD tweezers 120 mm form 2a stainless steel dissipative
- 5-067-13 ESD SMD tweezers 120 mm form 12 stainless steel, dissipative
- 5-068-13 ESD tweezers 120 mm form 13 stainless steel, dissipative
- 5-078-13 ESD SMD universal tweezers 130 mm form PSF stainless steel dissipative

