

Features

- Rotation Swivel
- Rubber
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

RS PRO Castor Wheels

RS Stock No.: 0631176



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Castors in zinc-chromium plated pressed steel, turning on double rim of balls. Rubber tyre flanged with thermoplastic material. Recommended use for office furnitures, metal furnishing, electrical household, etc.

General Specifications

Rotation	Swivel
Weight Class	
Load Capacity (Kg)	55
Load Capacity / 4pcs (Kg)	220
Tyre Material	Rubber
Hub Material	Thermoplastic
Bracket Material	Pressed Steel
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	

Operation Environment Specifications

Operating Temperature (Celsius)	
--	--

				
75x23	29	10,2	105	55

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	75
Wheel / Tread Width (mm)	23
Overall Height (mm)	105
Number of Fixing Holes	1
Fixing Hole Size (mm)	10,2
Hub Bearing Type	Plain Bore
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	
Levelling Extent (mm)	
Offset (mm)	
Castor Weight (Kg)	0.255

Fixing Centres Specifications

Fixing Centres (mm)	
Fixing Centres Length (mm)	
Fixing Centres Width (mm)	

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	
Fixing Plate Length (mm)	
Fixing Plate Width (mm)	