

METAL CIRCULAR SAW XR 18V 5AH LI-ION BRUSHLESS 184 MM - POWERSTACK

PERFORMING

- Cutting depth and power with brushless motor
- Clean cut to reduce the need for deburring
- Collect the chips as they are cut

PRACTICE

- Viewing windows with light for clear visibility of the blade
- Stainless steel sabot with measuring marks
- Optimized protection for better visibility of the blade
- Upper blade guard easy to remove to monitor the level of harvested chips

PRECISE

- Adjusting the cutting depth to fit any application
- Adjusting the rear protection for irregular profiles and in diving
- ERGONOMIC for maximum control
- Balanced, light (magnesium parts)
- Overmolded rear grip for maximum grip and increased control
- Ergonomic front handle

SECURED

- Push lock button to prevent accidental starts
- Quick and easy blade change



TSTAK box booklet - 2 batteries 18V 5Ah
Powerstack (DCBP518) - Charger (DCB1104) - 48
teeth blade (TCT)

DCS383H2-QW

5 035 048 808 108