

Hedge Trimmer LXT®

DUH751

18V • 750 mm • 0 – 4 400 min⁻¹

Model DUH751 is an efficient brushless trimmer powered by a 18V Li-Ion battery.

A cordless hedge trimmer with a brushless motor and a 750 mm blade for gardening. Two-handed safety switches offer added safety, and the tool has low noise levels. Three speed settings to suit different applications



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Strokes per Minute (SPM)	2000 / 3600 / 4400 min ⁻¹
Length Of Blade	750 mm
Max blade opening	23,5 mm
Tooth Spacing	35 mm
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	≤ 2,5 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²
Product Dimensions (L x W x H):	1261 x 225 x 192 mm

User benefits

- Brushless maintenance-free and long-life motor
- Double action switch for increased safety
- Variable speed
- Constant speed control maintains constant speed under load
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electric brake for maximum productivity and increased operator safety
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Optimum blade shape for smooth cutting and long run time

Link to product - www.makita.uk.com



Related products

■ Optional AC

197439-7

Grease Vessel Set



■ Other

User manual

Parts drawing