







S39MH

1/4" Square Drive Socket Set with Metric Bi-hex Profile and Screwdriver Bits/Bit Holder - 39 Pcs

PRODUCT DETAILS

- 6-Piece 1/4" Bi-hex sockets 6, 7, 8, 10, 11 and 13 mm A6700DM
- One 1/4" compact length metal handle ratchet, quick release, 60 teeth/6° action angle, 125 mm 6950MHS
- One 1/4" adaptor 60 mm KM653-QR
- One 1/4" bit holder with locking spring 6973A
- One 1/4" bit square adaptor to 1/4" hexagon K6625-1/4
- Three 1/4" bits, PH1, PH2, PH3
- Three 1/4" bits, PZ1, PZ2, PZ3
- Four 1/4" Hexagonal bits, H3, H4, H5, H6
- Four 1/4" Flat bits, 4, 4.5, 6.5, 8
- Eight 1/4" Torx bits, T8, T10, T15, T20, T25, T27, T30, T40
- Seven 1/4" Torx Tamper bits, TR10, TR15, TR20, TR25, TR27, TR30, TR40
- Micro matte finish
- High-performance alloy steel
- Less wear and damage to fastener thanks to Dynamic-Drive™ profile sockets
- Quick socket release button on ratchet
- Case: High density polythene (HDPE), 35 mm x 165 mm x 85 mm, SPAR-CASE-A6
- Standards: ISO 1174 and DIN 3120

PRODUCT ATTRIBUTES

Product				
S39MH	160 mm	85 mm	35 mm	570 g

Follow the Fish!

