

FEATURES

- Non-slip main handle and low
- Provides two-hand grip in the final phase of crimping
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear miscrimps and obstructions
- Precision eccentric adjustment
- Each tool has a unique serial number for traceability
- Durable: lifespan exceeds 50000 cycles
- High strength, through hardened alloy Swedish steel construction

RS PRO Plier Crimping Tool for BNC, TNC

RS Stock No.: 447-459



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

The 447-459 is an "Original line" hand crimp tool for SMA, SMB, SMC connectors. Producing 3.25 mm, 4.52 mm, 1.69 mm/.128", 0.178", and 0.067" hexagon shaped crimps, with the minimum of effort, either right or left handed.

General Specifications

Crimp Tool Type	Plier
Crimp Connector Type	BNC, TNC
Crimp Profile	Hexagon
Applications	Maintenance & repair, Electrical Installations, Cable assemblies

Mechanical Specifications

Overall Length	195mm
Width	18mm/0.71"
Height	59mm/2.32"
Wire Size (mm²)	RG122/U, RG174A/U, RG179B/U, RG180B/U, RG187A/U, RG188A/U, RG279/U, RG303/U, RG316/U
Crimping Force	7000N
Life span, cycles	50000
Weight	350g/0.75 lb
Crimp nest	3.25 mm / .128" 4.52 mm / .178" 1.69 mm / .067"
Handle spread (closed)	65mm
Handle spread (open)	130mm
Maximum handle force	400N
Standard Die Length	24mm
Standard Die width	10mm
Standard Die Height	10mm



Dimensions: (mm)



