

## Datasheet

# RS Anticorrosive Fluorescent Site Light, Fluorescent Tube, 58 W, 110 V IP65

**Stock Number - 670-2733**



### 110V Fluorescent Anti Corrosive Site Lights

Designed for temporary site installation

High impact corrosion resistant yellow polycarbonate body

Polycarbonate cover with prismatic light control

Uses a single 5ft (1600mm) 58W T5 fluorescent tube (not supplied, see 656-1309)

Emergency option has a 3 hour duration

Anti-corrosive	Yes
Height	360mm
IP Rating	IP65
Lamp Type	Fluorescent Tube
Length	1600 mm
Voltage Rating	110 V
Wattage	58 W
Width	240 mm