



**INNOVATION  
2014**

**A DUNLOP® INNOVATION  
DESIGNED EXPLICITLY FOR THE  
FOOD PROCESSING INDUSTRY**

- **COMFORT**
- **HYGIENE**
- **SAFETY**

**THE ULTIMATE PERFORMANCE IN PROTECTION AND COMFORT**

# FOODPRO

**The first real food boot!**

Dunlop® introduces a new generation of Purofort® boots for the Food Processing segment Industry. The mould of this boot has been specifically developed for food processing. Therefore the boot offers, in addition to all the benefits of Purofort® Technology, solutions based on the specific endusers needs within the Food Processing Industry.

## What makes FoodPro the Best?

### Comfort

- Specifically designed for orthopedic insole
- Gender specific design
- Purofort® Technology: light and flexible

### Hygiene

- Extra smooth design and shaft: easy to clean
- Various colours: preventing cross-contamination
- Anti-Bac Lining

### Safety

2 slip-resistant outsoles (SRC):  
The best slip resistance for each situation

- EN ISO 20345:2011 S4 CI SRC



## HYDROGRIP

Wet contaminated areas



## MULTIGRIP

(Semi-)solid contaminated areas



## Product specifications CA61131

### General

Description	<b>Dunlop FoodPro Purofort MultiGrip safety</b>	Size range/#	<b>35/36-49/50/14</b>
Upper/Sole Color	<b>White (ultra)/Blue</b>	Insole	<b>Dunlop extra thick PU insole</b>
Status	<b>Stock</b>	Lining	<b>Red Branded PU Lining</b>
Segment	<b>Food</b>	Resistance Code	<b>6</b>

### Safety

Standard	<b>EN ISO 20345:2011 S4 CI SRC</b>	<input checked="" type="checkbox"/> <b>Antistatic</b>	<input checked="" type="checkbox"/> <b>Cold insulating</b>
Safety marking manual	<b>Dunlop EN manual</b>	<input checked="" type="checkbox"/> <b>Oilresistant sole</b>	
	<input checked="" type="checkbox"/> <b>Steel Toecap</b>		
	<input checked="" type="checkbox"/> <b>Energy absorbing</b>		

### Packaging

Size	Boxtype	Polybag			Pairs/Box	Boxes/layer	#Layers	Pallet height
		Length	Width	Height				
<b>48-49</b>	<b>NL6</b>	<b>590</b>	<b>440</b>	<b>355</b>	<b>5</b>	<b>4</b>	<b>4.5</b>	<b>1.92</b>
<b>44-47</b>	<b>NL6</b>	<b>590</b>	<b>440</b>	<b>355</b>	<b>6</b>	<b>4</b>	<b>4.5</b>	<b>1.92</b>
<b>42-43</b>	<b>NL20</b>	<b>590</b>	<b>400</b>	<b>325</b>	<b>6</b>	<b>4</b>	<b>5</b>	<b>1.79</b>
<b>39-41</b>	<b>NL19</b>	<b>590</b>	<b>400</b>	<b>305</b>	<b>6</b>	<b>4</b>	<b>6</b>	<b>2</b>
<b>35/36-38</b>	<b>NL18</b>	<b>530</b>	<b>400</b>	<b>290</b>	<b>6</b>	<b>4</b>	<b>6</b>	<b>1.91</b>