

Universal - AS*3*1F-A AS1311F-M5-06A

Datasheet

General series information

- Port Size: M5, 10-32 UNF, 1/8, 1/4, 3/8, 1/2
- Applicable Tubing O.D.: Ø 3.2 to Ø 16 mm and Ø 1/8" to Ø 1/2"
- Operating Pressure Range: 0.1 to 1 MPa.

Standard specifications

Pressure medium	Compressed air
Maximum temperature of pressure medium	60 °C
Minimum temperature of pressure medium	-5 °C
Maximum ambient temperature	60 °C;60 °C
Minimum ambient temperature	-5 °C
Weight	0.006 Kg

Additional information

Catalogue

[AS-1F_FG-A-Dd_EU.pdf](#)